

NOTE: A full range of ASD pipes and fitting are available.



Manual ball valve

SEC-MV-25-PVC

SEC-MV-25-ABS

Manual ball valve for revision and cleaning works with compressed air.

| Technical data | |
|---------------------------|-------|
| Material: | PVC |
| Pipe connection diameter: | 25 mm |



Detector Box

SEC-REK 511

For the localization of a fire in a separate room, when a single SEC-ASD is monitoring several rooms. To use together with the SSD 515-Xs smoke detector. Has to be installed in every stub, which leads to a single room from the main tube.

| Technical data | |
|-------------------------|-------------------|
| Operating voltage: | 18-28 VDC |
| Ambient temperature: | 0 °C to + 50 °C |
| Dimensions (H x W x D): | 186 x 122 x 85 mm |



Scattered light smoke detector for SEC-REK 511

SEC-SSD-515-1S sensitivity 1.2%/m
SEC-SSD-515-2S sensitivity 0.6%/m
SEC-SSD-515-3S sensitivity 0.3%/m

| 18 to 28VDC |
|-------------------|
| -20 °C to + 60 °C |
| IP 44 |
| white |
| 80 x 56mm |
| |

The SSD 515-xS (Scattered Light Smoke Detector) is the smoke sensor for the accessory device SEC-REK 511 (full addressing) for the Aspirating Smoke Detector of the SEC-ASD and RAS product family. The SSD 515-xS operates according to the scattered light principle and is designed so that it optimally meets the specific requirements of smoke detection in association with an Aspirating Smoke Detector. The detector has alarm threshold tracking and is additionally available with various sensitivities. By choosing the appropriate detector sensitivity, application-specific detection properties of the Aspirating Smoke Detector are possible.



Filter box small

SEC-FBS-25-PC

Filter box small including filter-mat. Inserted into the sampling pipe before SEC-ASD. To be used in slightly dusty rooms.

| i ecnnicai data | |
|---------------------------|-----------------|
| Dimensions (H x W x D): | 80 x 82 x 85 mm |
| Material: | PC |
| Pipe connection diameter: | 25 mm |



Filter mat small for filter box small

SEC-FBS-25-PC-EFM-5er

Filter-mat for filter box small. Packaging of 5 pieces

| Technical data | |
|-------------------------|-----------------|
| Dimensions (H x W x D): | 80 x 80 x 20 mm |



Filter box large

SEC-FBL-25-PC

Filter box large including filter-mat. Inserted into the sampling pipe before SEC-ASD. To be used in dusty rooms.

| Technical data | |
|---------------------------|-------------------|
| Dimensions (H x W x D): | 120 x 122 x 85 mm |
| Material: | PC |
| Pipe connection diameter: | 25 mm |
| | |



Filter mat large for filter box large

SEC-FBL-25-PC-EFM-5er

Replacement filter mat for the filter box large. Packaging of 5 pieces

| Technical data | |
|-------------------------|------------------|
| Dimensions (H x W x D): | 117 x 80 x 80 mm |
| | |