

### Sampling point with heating



- SEC-HEAT-3.0-PVC** red
- SEC-HEAT-3.5-PVC** blue
- SEC-HEAT-4.0-PVC** green
- SEC-HEAT-4.5-PVC** black
- SEC-HEAT-5.0-PVC** brown

To install the aspirating pipe in deep-freeze rooms to prevent the freezing of the aspirating holes. HEAT X.X is the relevant diameter for SEC-ASD PipeFlow-calculations (3.0/3.5/4.0/4.5/5.0mm)

#### Technical data

|                  |              |
|------------------|--------------|
| Pipe connection: | 25 mm        |
| Hole Diameter    | Type         |
| 5,7 mm           | HEAT 3.0 PVC |
| 6,1 mm           | HEAT 3.5 PVC |
| 6,3 mm           | HEAT 4.0 PVC |
| 6,7 mm           | HEAT 4.5 PVC |
| 7,1 mm           | HEAT 5.0 PVC |

### Sampling point with heating



- SEC-HEAT-3.0-ABS** red
- SEC-HEAT-3.5-ABS** blue
- SEC-HEAT-4.0-ABS** green
- SEC-HEAT-4.5-ABS** black
- SEC-HEAT-5.0-ABS** brown

Same as HEAT X.X PVC but in ABS.

#### Technical data

|                  |              |
|------------------|--------------|
| Pipe connection: | 25 mm        |
| Hole Diameter    | Type         |
| 5,7 mm           | HEAT 3.0 ABS |
| 6,1 mm           | HEAT 3.5 ABS |
| 6,3 mm           | HEAT 4.0 ABS |
| 6,7 mm           | HEAT 4.5 ABS |
| 7,1 mm           | HEAT 5.0 ABS |

### Heat Resistor



#### SEC-Heat-Resistor

Replacement for the sampling point with heating HEAT X.X PVC/ABS.

#### Technical data

|           |       |
|-----------|-------|
| Resistor: | 220 Ω |
|-----------|-------|

### Cable connection fitting



#### SEC-CCF-25-PVC

#### SEC-CCF-25-ABS

Cable connection fitting set for T-junctions of the tubes in deep-freeze rooms.

#### Technical data

|                           |       |
|---------------------------|-------|
| Pipe connection diameter: | 25 mm |
|---------------------------|-------|

### Silicon litz wire



#### SEC-SLW-0.5-wt (white)

#### SEC-SLW-0.5-bk (black)

Silicon litz wire 0.5mm<sup>2</sup> to connect the heating resistors in the heating nozzles HEAT X.X PVC/ABS.

Order quantity must be a multiple of 100.

#### Technical data

|                 |            |
|-----------------|------------|
| Length:         | 1 m        |
| Packaging unit: | 100 pieces |

### Wiring connection unit



#### SEC-WCU-535

For the introduction of the supply of the sampling point with heating into the aspirating tube, with internal clamps. For more details please see the guidelines for deep freeze-warehouses.

#### Technical data

|                           |                 |
|---------------------------|-----------------|
| Dimensions (H x W x D):   | 80 x 82 x 85 mm |
| Material:                 | PC              |
| Pipe connection diameter: | 25 mm           |
| Weight:                   | 317g            |